

TECHNICAL DATA SHEET

CONCENTRATE FOR EPOXY AND POLYURETHANE RESINS

TUBALL™ MATRIX 301 is a conductive additive based on a surfactant for solvent-free epoxy and PU coatings without drawbacks in color and mechanical properties. Also recommended for epoxy composites. TUBALL™ MATRIX 301 is available in flakes with a pasty texture form.

TUBALL™ is a unique graphene nanotube additive from OCSiAl that provides electrical conductivity at ultra-low dosage with minimal impact on the rheological and mechanical properties of the host matrix.

APPLICATIONS

- Anti-static flooring;
- Composite anti-static pipes;
- Anti-static composite materials and compounds;
- Other applications where electrical conductivity is required.

BENEFITS

- TUBALL™ MATRIX only requires an ultra-low dosage starting from just 0.1 wt.%;
- Allows production of conductive parts that retain bright colors;
- Maintains or even increases mechanical strength;
- Ensures permanent and uniform electrical conductivity without “hot spots”.

PROPERTIES


CONCENTRATE CARRIER		ETHOXYLATED ALCOHOL
PROPERTY	TEST METHOD	VALUE
Flash point	ASTM D3278	190°C
Density at 25°C	ASTM D4052	0.97 g/ml
Hydroxyl value	ASTM E1899-08	100 mg KOH/g
Moisture	OCSiAl internal	<1 wt.%

TUBALL™ MATRIX 301 may contain particles up to 500 µm in size; the mass concentration of such inclusions does not exceed 0.04%.

TYPICAL ADDITION RATE

Depending on the characteristics of the dilution polymer and the processing conditions, the loading range of TUBALL™ MATRIX 301 for anti-static or dissipative applications can be as low as 0.1–4.0 wt.%. The exact loading level depends on the required performance, resin characteristics, processing conditions and presence of other ingredients.

An example of a percolation curve, obtained by compounding TUBALL™ MATRIX 301 in D.E.R. 351 epoxy resin, is shown in the figure below. The dilution of the concentrate in neat D.E.R. 351 was performed using a mechanical overhead stirrer.



DILUTION

In order to obtain a high-quality TUBALL™ MATRIX dispersion, OCSiAl recommends that close attention be paid to the dilution procedure. Refer to the Processing Guidelines for detailed information.

PACKAGING

OCSiAl provides TUBALL™ MATRIX 301 samples in plastic containers (50 g concentrate). Industrial volumes are available in different packaging up to 50 kg.

STORAGE AND TRANSPORTATION

The product is stable in unopened original packaging when stored at temperatures below 70°C. The recommended storage life is up to 24 months when stored as directed.

SAFETY

To ensure safe handling, the appropriate safety regulations should be observed. OCSiAl recommends that every user should be able to apply the safe handling procedures necessary for the user's applications before any handling or manufacturing takes place. A Safety Data Sheet outlining the hazards and handling methods for TUBALL™ MATRIX 301 is available.

WARRANTIES AND DISCLAIMER

The Products correspond to the chemical composition indicated in the Technical Data Sheet and the Safety Data Sheet supplied with the Product. The information contained in this document (Information) is based on trials carried out by OCSiAl and may contain inaccuracies or errors that could cause injury, loss or damage.

OCSiAl gives no further warranty and makes no further representation regarding the Products and/or the accuracy of Information and/or suggestions for any particular use of the Products or Information, or that suggested use will not infringe any patent. The Products and Information are supplied on an “as is” basis. These express provisions are in place for all warranties, representations, conditions, terms, undertakings and obligations implied by statute, common law, custom, trade usage, course of dealing or otherwise (including implied undertakings of satisfactory quality, conformity with description, fitness for purpose and reasonable skill and care), all of which are hereby excluded to the maximum extent permitted by applicable law.

CONTACT INFORMATION

ASIA		EUROPE	NORTH & SOUTH AMERICA
KOREA 208, Gaetbeol-ro 12, Yeonsu-gu, Incheon, 21999, Korea +82 32 260 0407 asiapacific@ocsial.com	CHINA #2004, 20th floor, Tower B, Da Chong Business Centre, Yue Hai Street, Nanshan District, Shenzhen, Guangdong, China +86 755 867 00059	JAPAN Tokyo, Japan 070-1421-0331 japan@ocsial.com	LUXEMBOURG 1 Rue de la Poudrerie, L-3364, Leudelange, Grand-Duché de Luxembourg +352 27990373 europe@ocsial.com
HONG KONG Room 1102, 11/F, Lippo Sun Plaza, 28, Canton Road, Tsim Sha Tsui, Kowloon, Hong Kong +852 3575 3946	Ground floor, Unit 4, Building 7, No.160, Basheng Road, Pudong district, Shanghai, China +86 135 9012 5295 china@ocsial.com	INDIA Vimal intertrade PVT Ltd, Shivam centrium, Sahar road, Koldongri, Andheri East, Mumbai, 400 069, India + 91 22 6288 4200 india@ocsial.com	USA 500 S Front St, Suite 860, Columbus, OH 43215, USA +1 415 906 5271 usa@ocsial.com